



Accu-Sep

Designed with multi-stage separations for real-world, 24 hour continuous operation.

Sized and designed to operate in most ambient conditions year-round.

No electricity required.



Features

Constructed of all non-corrosive materials

Gravity activation

Diffuser has multiple inlets, the entire assembly can be rotated

Removable access lid

Translucent oil container collects de-emulsified oil

Red flow indicator

Sample and reference jars

Benefits

Easily maintained with low maintenance costs

No electricity required - no moving parts

Makes installation more convenient

Easy entry to the Pre-Adsorption Chamber and the Carbon Media

Can be easily monitored

A visual alert that service is required

Quick evaluation of the clean condensate, ensures proper operation

Model Nos. AS15, AS30, AS60,
AS90, AS120S, AS180S, AS240S

How it Works

The Accu-Sep utilizes multi-stage separations technology to remove lubricating oils from condensate streams. In the first stage, the sediment chamber collects and helps prevent rust, dirt, and scale from migrating into the main reservoir. The second stage is the large main reservoir, which provides sufficient residence time to allow oil to coagulate and float to the surface. Next, the pre-adsorption chamber removes the segment of oils that are still in the solution or have migrated through to this chamber. In the final stage, the carbon beds ensure that the condensate will meet or exceed the discharge limits.



Dimensions

Model	Max. CFM Capacity*		Height	Depth	Width	Dry Weight Lbs.
	90°F/90%RH					
AS15	150		30"	19"	26.5"	50
AS30	300		39"	21"	34"	90
AS60	600		39"	31"	35"	170
AS90	900		45"	31"	35"	229
AS120	1200		39"	31"	72"	240
AS180	1800		39"	31"	109"	360
AS240	2400		39"	31"	146"	480

* The maximum CFM capacity ratings listed may be increased by 25% if a refrigerated air dryer is not used. Refer to Accu-Zorb and Posi-Zorb for use with emulsified lubricants such as polyglycols. Please contact your local Distributor or the Factory for proper sizing when using other types of lubricants and/or compressors.

Visit
airsyspro.com/selector-guide
to use our
Condensate Separator Guide



AIRTEC GLOBAL LLC
1100 NW Loop 410 Ste. 764
San Antonio, TX 78213
Phone: (210) 366-8805
Email: support@airtec.global
<http://airtec.global>

All design specifications are subject to change without notice.
© 2017 FGA-030-072817-02